

Booth
#4004



Lubricare

This handpiece maintenance device offers sprays specifically designed for separate phases of the maintenance cycle: Spraynet, for dissolving impurities and cleaning; and Lubrifluid, for lubrication of instruments. The device holds up to 4 instruments per cleaning cycle, while cycles take 25 seconds per instrument with two choices of cleaning and lubrication modes.

Bien-Air USA Inc.
800-433-BIEN | bienair.com
CIRCLE RS NO. 32

Booth
#600,
5037,
5327



NewTom VG3

Offering a dynamic, single-rotation field of view, the VG3 is said to be an important contribution to the high-performance field of view offered by its predecessor, the VGi. A modular hybrid 2D/3D system, the VG3 can start as a 2D system that is upgradable at any time to include a cephalometric sensor or 3D cone beam computed tomography with an 11" x 8" field of view.

BIOLASE
888-424-6527 | biolase.com
CIRCLE RS NO. 33

Booth
#1200



eCEMENT™

eCEMENT offers a light-cure and dual-resin cement to ensure lithium disilicate restorations provide long-term retention of single or multiple restorations, as well as shade stability. Additionally, the radiopaque cement offers easy placement of lithium disilicate veneers, onlays, crowns, three-unit bridges and inlays.

Bisco
800-247-3368 | bisco.com
CIRCLE RS NO. 34

Booth
#5206



Perfectemp 10

This material's 10:1 automix formula results in a minimal oxygen-inhibited layer for better handling and polishability, plus it provides high compressive and flexural strength. 3.4% shrinkage is said to offer an accurate fit and marginal integrity, while the material's multiple uses make it well suited for a wide range of highly esthetic restorations.

DenMat
800-4DENMAT | denmat.com
CIRCLE RS NO. 35

Booth
#2600,
2800



TPH Spectra™ Universal Composite

This composite provides the handling preference of choice, while a reduction in shades allows for carrying less inventory in the office. Plus, it is said to provide confidence that the chameleon shading ability of the composite will blend into the surrounding tooth structure, making the restoration indistinguishable.

DENTSPLY Caulk
800-532-2855 | tphspectra.com
CIRCLE RS NO. 36

Booth
#2600,
2800



Midwest® Automate™

This 4-port automated handpiece maintenance system reportedly offers accurate and consistent cleaning, lubricating and expelling. Plus, all-steel construction is said to offer durability for a longer life, while a dedicated chuck cleaning port cleans and lubes the handpiece chucking mechanism for simpler insertion and extraction of cutting instruments.

DENTSPLY Professional
800-989-8825 | professional.dentsply.com
CIRCLE RS NO. 37